

IC 7300 Settings for Digital

Connector Settings

VA7FI has the following settings on his radio. The settings in grey are there for reference only and can be different.

MENU > SET > Connectors:	
ACC/USB Output Select	AF
ACC/USB AF Output Level	40%
ACC/USB AF SQL	OFF (Open)
ACC/USB AF Beep Speech... Output	OFF
ACC/USB IF Output level	50%
ACC MOD Level	50%
USB MOD Level	40%
DATA OFF MOD	MIC
DATA MOD	USB
MENU > SET > Connectors > CI-V:	
CI-V Baud Rate	Auto
CI-V Address	note it
CI-V Transceive	ON
CI-V USB→Remote Tx Address	N/A
CI-V Output (for ANT)	OFF
CI-V USB Port	Link to [REMOTE]
MENU > Set > Connectors:	
USB Serial Function	CI-V
MENU > Set > Connectors > USB SEND Keying:	
USB SEND	RTS
USB Keying (CW)	OFF
USB Keying (RTTY)	OFF
Inhibit Timer at USB Connection	ON

Filter Settings

To adjust the filter width:

- Press FIL1 (or FIL2 or FIL3) button at the top of the screen (above frequency) until it says FIL1.
- Press and hold FIL1 (yes, the same button as before).
- Press the **BW** button and turn the VF0 knob until it says "3.6k"
- Then turn the TWIN PBT knob (top left) to adjust the boundaries to 600 and 2600 (the picture shows 650 and 3400). This step can be tweaked anytime on the fly to filter out unwanted signals at the edge of the band. This is useful if say you've got strong RTTY signals activating your **AGC**, thus reducing the strength of the signals you're interested in.
- Optionally, press FIL1 again to also customize FIL2 and FIL3.
- When done, press the **MENU** button and select the screen you usually like to see (SCOPE, METER, etc)



ACG Adjustments

- Pick a clear frequency.
- Press **FUNCTION** button.
- Press and hold the AGC button.
- Select the FAST button and turn the VFO knob until it reads OFF.
- Optionally, set the MID to 0.3s and the SLOW to 2.0s.
- Press <MENU> and select SCOPE, or METER, or ...

Digital and Voice settings

Mode	Digital	Voice
Default Frequency	7.078.00 USB-D	3.739.00 LSB
MUTI (select and turn the knob)		
RF POWER	30%	100%
MIC GAIN	40%	40%
COMP	N/A	ON 4
MONITOR	ON 100%	OFF 100%
FUNCTION		
P.AMP ATT	OFF	OFF
AGC	OFF	SLOW
NOTCH	OFF	OFF
NB	OFF	ON
NR	OFF	OFF
IP+	OFF	OFF
VOX	OFF	OFF
COMP	N/A	ON
1/4	OFF	WIDE
MONI	ON	OFF